

DESIGN OF THE HIGH GRADIENT NEGATIVE HARMONIC STRUCTURE FOR COMPACT ION THERAPY LINAC*

S.V. Kutsaev, R. Agustsson, A.Yu. Smirnov, A. Verma, RadiaBeam Systems, LLC A. Barcikowski, R. Fischer, B. Mustapha, Argonne National Laboratory

ABSTRACT:

A novel concept for an Advanced Compact Carbon Ion Linac (ACCIL) that will deliver up to 1 pnA of carbon ions with variable energy from 45 MeV/u to 450 MeV/u in a 45m footprint, has been developed by Argonne National Laboratory (ANL) in collaboration with RadiaBeam. The ACCIL will have a 35 MV/m real-estate accelerating gradients that became possible to achieve with the development of novel S-band high-gradient structures, capable of providing 50 MV/m accelerating gradients for particles with β >0.3. In particular, a β =0.3 structure based on the novel approach of operation at the first negative spatial harmonic with the increased distance between the accelerating gaps will be presented. This is the first attempt to reach such high gradients at such small velocities. RadiaBeam and ANL have demonstrated the feasibility of building this structure for accelerating carbon ions by means of advanced computer simulations and are currently working towards the fabrication of this structure for high power tests..

Coupled-DTL CCL DTL (6-gaps per each) 19 tanks @ 2856 MHz (65 gaps) 10 tanks @ 952 MHz 19 tanks @ 2856 MHz ECR IS 476 MHz 476 MHz 20 MeV/u 45 MeV/u 25 m

ACCIL: Advanced Compact Carbon Ion Linac

Higher Spatial Harmonics Structure

- Periodic structures have an infinite number of spatial harmonics.
- These harmonics have the same frequency but different spatial field distribution.
- An accelerating structure can be designed for the first negative harmonic m=-1 instead of the fundamental harmonic m=0
- Larger period allows implementing noses for higher shunt impedance



90% of energy is gained in S-band High Gradient Section:

- Operating frequency f = 2856 MHz
- Phase velocity $\beta = 0.3 0.7$
- Accelerating gradient 50 MV/m, constant along the section
- Aperture diameter 2a = 6 mm
- Beam pulse width $\tau = 0.5 \ \mu s$
- Repetition rate F = 120 Hz

P. Ostroumov et al., "Compact Carbon Ion Linac", NAPAC'16, Chicago, IL, 2016, MOA4CO04

Design Optimization

Number of holes	16	12	8	4	Group velocity, %c	0.45	0.30	0.15
Peak E-field, MV/m	155.5	156.0	155.4	155.7	Peak E-field, MV/m	155.2	155.5	155.6
Pulsed heating, K	19.78	20.51	22.48	27.8	Pulsed heating, K	24.7	21.5	17.54
Shunt impedance, MΩ/m	33.08	33.64	34.35	35.34	Shunt impedance, MΩ/m	32.3	33.1	34.2
Modified Poytning, MW/mm ²	1.08	1.17	1.38	1.90	Modified Poytning, MW/mm ²	1.68	1.39	1.02
Temperature gradient, K	14.8	13.34	12.37	11.06	Temperature gradient, K	11.9	10.7	9.5
Mechanical stresses, MPa	62.4	49.27	41.21	34.58	Mechanical stresses, MPa	37.0	32.8	29.0

- Reduced number of holes from 16 to 8
- Increased iris thickness from 2.5 mm to 3.0 mm
- Reduced peak power requirement from 42 to 37 MW
- Increased filling time from 350 ns to 500 ns

S.V. Kutsaev et al., "High-gradient low-β accelerating structure using the first negative spatial harmonic of the fundamental mode", Phys. Rev. Accel. Beams 20, 120401 (2017).

Summary:

The proposed acceleration with higher spatial harmonics has enabled the development of a novel high-gradient accelerating structure design for protons and carbon ions with low β . The prototype structure being developed will become the enabling technology for compact hadron therapy linacs. We have performed electromagnetic optimization of 50 MV/m β =0.3 NHS cell to achieve mechanical stresses below the annealed yield stresses of 52 MPa. The design of a robust cooling system and the careful structural analysis helped to ensure the stable operation at high gradients in long-term applications. The NHS section is currently being built and is planned to be tested in 2019.

- Improved thermal conductivity
- Reduced peak stresses by 40%

-1

18.375

5π/6

2.5

10.725

15

31.7

8065

0.26

0.42

0.3

50

156.5

1.3

28.2

15.6

59.6

Peak mechanical stresses, MPa



S. Kutsaev , "Compact High Gradient Ion Accelerating Structure", International Patent Application PCT/US2018/030980, 2018

Engineering Design

- Average RF power losses are 2.5 kW
- The structure is cooled with four cooling blocks
- Maximum average temperature rise is 18.2°C
- Maximum pulsed temperature rise is 19.8°C
- Pulsed von Mises stresses (45.8 MPa) are less than yield stresses of OFHC copper (54 MPa)
- Fatigue stress is 11.9 MPa
- Projected life is 10^{12} cycles \rightarrow life expectance is 320 years



RadiaBeam Systems is a leading supplier of accelerator-based X-ray sources, security systems, and irradiators as well as large-scale accelerator technology for the research community. Our products include turnkey sterilization systems for medical device manufacturer and food processors, industrial radiography systems, security systems, OEM accelerating structures, and light source insertion devices.

*This work was supported by the U.S. Department of Energy, Office of High Energy Physics, under Accelerator Stewardship Grant, Proposal No. 0000219678 and STTR grant DE-SC0015717 Visit us online at www.radiabeamsystems.com info@radiabeam.com 1713 Stewart Street | Santa Monica, CA | 90404 | USA



Title Here. Do not move box or resize

Authors Calibri Regular / size 36 / center aligned. Do not move or resize box

Section Titles: Calibri Bold / size 36

Regular Content: Calibri Regular / size 36Black text / Center aligned for full width / Full justified if in columns

Smaller sizes are acceptable - 24 pt should be the smallest

When choosing color, it should be RadiaBeam orange (RGB 239,129,50) Do not use RadiaBeam Blue on RBS posters

Provide at least 0.5 inches of space around any image – select box

Adjust box sizes as necessary

Section Titles: Calibri Bold / size 36 Regular Content: Calibri Regular / size 36 Black text / Center justified for full width / Full justified if in columns

YOU CAN ALSO WORK WITHOUT THE GREY BOXES.

Section Titles: Calibri Bold / size 36

Regular Content: Calibri Regular / size 36 Black text / Center justified for full width/ Full justified if in columns

You can also work full width. Left Justify if you like.

Section Titles: Calibri Bold / size 36 Regular Content: Calibri Regular / size 36 Black text / Center justified for full width / Full justified if in columns

You can also work with full width, with or without grey backgrounds.

REMOVE ORANGE LINE FOR FULL COLUMNS



RadiaBeam Systems is a leading supplier of accelerator-based X-ray sources, security systems, and irradiators as well as large-scale accelerator technology for the research community. Our products include turnkey sterilization systems for medical device manufacturer and food processors, industrial radiography systems, security systems, OEM accelerating structures, and light source insertion devices.

This work was supported by the U.S. Department of Energy, Office of High Energy Physics, under contract DE-SC0013684

Visit us online at www.radiabeamsystems.com info@radiabeam.com 1713 Stewart Street | Santa Monica, CA | 90404 | USA